NATURA B5 1.35

Countertop Water Purification System Cut Sheet



Dimensions	Refrigeration / Carbonation Unit (NWSB)	Filtration Kit (NWFS)
Depth	24.6" (625.5mm) including drip tray	6.0" (152.4 mm)
Width	12.6" (320.0 mm)	16.4" (417.0 mm)
Height	20.0" (508.0 mm) total height with faucets	14.4" (365.8 mm)
Weight	55 lbs (24.9 kg)	18 lbs (8.2kg)





Chilled Still



Chilled Sparkling

- Countertop System
- 35 L/Hr. Chilled Sparkling and Chilled Still Water
- Ideal for Restaurants, Hotels, Offices, Health and Wellness Spas, etc.

Technical Information		
Water Filtration System	3-Stage Filtration: Sediment; Carbon (Chlorine, Taste, Odor); Nanoceram (Lead & Cysts)	
Machine Configuration	Consists of 1 Filtration Kit (NWFS) + 1 Refrigeration / Carbonation Unit (NWSB)	
CO2 Cylinder (Not Provided By Natura)	Sold separately - connected with a 1/4" JG tubing and pressure regulator (included) to the refrigeration / carbonation unit (NWSB)	
Material	Stainless steel	
Maximum Chilled Carbonation Capacity	35 liters per hour	
Maximum Flow Capacity	150 liters per hour	
Avg. Time To Fill A One Liter Bottle	15 sec	
Standard Oper'g Water Supply Pressure Psi (bar) - regulated With A Pressure Regulator (included)	40 psi min 100 psi max. (2.75 - 6.9 bar)	
Electrical (Volts/Hertz/Amps)	110-120V / 60HZ / 6 AMPS (US) 220-230V / 50HZ / 2.5 AMPS (INT'L)	
Electric Power Consumption (approximate)	165 Watts Normal Oper'g /6 Watts Idle (US) 285 Watts Carbonation Oper'g (US) 170 Watts Normal Oper'g / 9 Watts Idle (INT'L) 290 Watts Carbonation Oper'g (INT'L)	







Technical Drawing

12.5 [317] REAR VIEW 12.6 [320] 2.125 [54]


LEFT SIDE

4.125

[105]

7.0

Filter Assembly



1. Water Supply:

16.375 [416]

- 1.1 Water supply shut-off valve that can adapt to a 3/8" compression fitting within 5' (1.5m) of the machine location
- **1.2** Shut-off valve that will only be used for the Natura unit. Neither the water line nor the shut-off valve can be shared with espresso machines, coffee makers, ice machines, etc.
- **1.3** Maximum inlet water temperature of 75°F (24°C). High temperature will affect chilled water capacity
- **1.4** Minimum inlet water flow rate of 2.2 gallons/min
- 1.5 Water pressure range: 45 PSI 120 PSI

2. Dedicated CO2 + Electrical Supply:

19.125 [486]

TOP VIEW

11.0

RIGHT SIDE

2.1 Dedicated CO2 canister on-site within 5' (1.5m) of machine location (standard tanks are 5–50 lbs UN1013 Food Grade gas)

5.5 [140]

17.875 [454]

2.2 Electrical supply available within 5' (1.5m) of machine location: 115V for B5/B5U/D5/D5U; 230V for B5i/B5Ui/D5i/D5Ui

3. For Bulk CO2 Connection Only (to be hooked up by CO2 supplier):


- **3.1** Dedicated CO2 connection line from the bulk CO2 canister requires the bulk tank to have a dedicated CO2 regulator
- **3.2** Dedicated CO2 connection line from bulk CO2 canister requires a different regulator (NOT SUPPLIED BY NATURA) within 5' (1.5m) of the machine location
- **3.3** Dedicated CO2 connection line from bulk CO2 canister requires a minimum pressure rating of 100 PSI
- **3.4** Dedicated CO2 connection line from bulk CO2 canister requires the pressure regulator set at 60 PSI. Setting higher than 60 PSI will damage the unit and void the warranty

Providing enough ventilation space:

- (a) 6.0" of clearance on both sides of the unit for ventilation
- (b) 2.0" of clearance in the back and front of the unit
- (c) 14.0" minimum clearance above the unit for removing the top to (i) perform routine maintenance and to (ii) enable technician to check water reservoir level during preventative maintenance visits

Note: Please remember to factor CO2 canister and Filtration Kit assembly into clearances.

Isometric View Required Clearance (Reference Only)



- 1. Natura B5 Water System
- 2. Filtration Kit
- 3. Water Line (not provided)
- 4. C02 Tank (not provided)





3 Stage Filtration System



Unfiltered Water In

Stage 1

A 5-micron spun polypropylene sediment filter traps large particles sediment, dirt and silt.

Stage 2

A 0.5-micron high flow carbon filter reduces chlorine, taste and color. Certified to NSF 53 for the reduction of containments.

Stage 3

Natura uses a NASA-derived technology that utilizes electroposititve attraction to further reduce bacteria, viruses, various chemicals and soluble organics. Purified, Filtered Water Out

Contact sales@naturawater.com · service@naturawater.com · +(877)302-8638 · www.naturawater.com