




**GENESIS
INTERNATIONAL**

SHERLOCK

SOLID STATE (CMOS) REFRIGERANT GAS SENSOR



SHERLOCK CMOS SENSOR

GENERAL

SHERLOCK CERAMIC METAL OXIDE SEMICONDUCTOR (CMOS) REFRIGERANT GAS SENSOR was designed to detect for the presence of a refrigerant gas within an enclosed space. The sensor is mounted within the space to be monitored and connected by cable to the monitoring device. Each sensor is calibrated to a clean air base zero level at the factory prior to shipment. There are three models of the CMOS sensor, a general one for HCFC/HFC and HFO gases, including the new A2L refrigerants. Also a separate one for Ammonia. The CMOS Sensor should be utilized as a signal source for a **SHERLOCK** Refrigerant Gas Monitoring System, *Wizard* Evaporator Control or **Walk-In** Monitor & Control.

**** Please Note: Sensor Part Numbers Have Changed for Several Refrigerants, See the Sensor List on the 2nd Page ****


APPLICATIONS

Typical applications include:

- Refrigerated Rooms
- Wineries
- Bakeries
- HVAC Chiller Equipment Rooms
- Refrigeration Mechanical Rooms
- Food Processing Plants

SPECIFICATIONS

ENCLOSURE RATING	NEMA1
DIMENSIONS Inches (mm)	4.3 x 2.4 x 1.2 (109 x 61 x 31)
POWER INPUT	12VDC, 250 mAMPs
OUTPUT (Genesis Control Only)	0.5 - 5 VDC
EFFECTIVE RANGE	20 to 1000 ppm, Control and Refrigerant Gas Type Dependent
ACCURACY	±10% to 50% of reading (Gas Dependent, Could be higher for some newer blends)
REPEATABILITY	±10% when proper calibration and Maintenance is followed.
AVAILABLE GAS SENSORS	HCFC, HFC, HFO & Ammonia
OPERATING ENVIRONMENT	
TEMPERATURE	-25 to 120° F (-32 to 49°C)
HUMIDITY	0 TO 85% RH Non-Condensing
CALIBRATION	Every 6 Months
WARM-UP TIME	Reading will stabilize after several hours
LIFE EXPECTANCY	Average of 3 to 5 years in normal environments



CMOS SENSOR SELECTION CHART*

Model 82-0101-10 -- HCFC/HFC gases

R-22	R-404A(HP62)	R-413a
R-123	R-405A(G2015)	R-438a
R-125	R-406A(CHG)	R-434a
R-134a	R-407A	R-448a
R-143a	R-407B	R-449a
R-152a	R-407C	R-503
R-400	R-407D	R-507A(AZ50)
R-401A(MP39)	R-408A(FX10)	R-508A
R-401B(MP66)	R-409A(FX56)	R-508B(SUVA95)
R-401C(MP62)	R-410A(AZ20)	R-509A(TP5R2)
R-402A(HP80)	R-410B	R-513A
R-402B(HP81)	R-411A	R-514A
R-403A	R-411B	
R-403B	R-412A(TP5R)	

Model 82-0645-10 -- HFC/HFO gases

R-22	R-454A	R-1233ZD(e)
R-32	R-454B	R-1233ze
R-125	R-454C	R-1234yf
R-290	R-514A	R-1234ze
R-404a	R-515A	
R-410a	R-515B	

Model 82-0102-10 -- Ammonia


R-717

THE BELOW SENSORS WILL HAVE LIMITED DETECTABILITY USING THE 82-0101-10 OR THE 82-0102-10 CMOS

R-11	R-23	R-142B
R-12	R-113	R-500(AZ50)
R-13	R-124	R-502

* Please Note: Sensor Part Numbers Have Changed for Several Refrigerants

TYPICAL WIRING DIAGRAM



NOTE: These sensors, due to their nature, are susceptible to detection of non-refrigerant gases and cannot distinguish the presence of different refrigerant gases, only that there is a gas present. The CMOS sensor will detect concentrations of gasoline, diesel, and propane exhaust and fumes from solvents, paints, cleansers, and others (Please call Genesis Customer Support for more information.) The stated accuracy is a best case and some refrigerant blends can be off as much as 50 to 100% of the Sherlock Control ppm reading.

NOTE: The stated average life expectancy for this sensor is 3 to 5 years, however, continued exposure to refrigerants and other gases and humidity and other adverse conditions can severely decrease sensor life.



GENESIS INTERNATIONAL

1040 Fox Chase Industrial Dr.

Arnold, MO 63010

Tel: 636-282-0011

Fax: 636-282-2722

Web: www.Genesis-International.com

E-Mail: Mail@Genesis-International.com