





HYDRAULIC INSTALLATION, HB-200

DRAWING NO. 10-0204 REV.

| REF. | QTY | PART NO. | PART DESCRIPTION | COMMENTS |
|------|-----|--------------------|------------------------------|------------|
| 1 | 2 | AD 4250-15 | FEMALE QUICK COUPLER | |
| 2 | 4 | HD RSE.06X1.387 | SNAP RING, EXTERNAL | |
| 3 | 2 | RE PN-1X288 | ARM ROD END PIN | 100 SERIES |
| 4 | 2 | HD PC 1X2-3/4 | ARM BASE END CLEVIS PIN | GREEN CYL |
| 5 | 2 | HD HPC.178 | ROLL PIN, ARM BASE END | |
| 6 | 1 | CY EN250-PA | PASSENGER ARM CYLINDER | GREEN MFG |
| 7 | 1 | CY EN275-DA | DRIVER ARM CYLINDER | GREEN MFG |
| 8 | 2 | HD ZG 1/4-28 STR | GREASE ZERK | |
| 9 | 1 | HA 6M3K-43.5 | QC TO PASSENGER ARM CYLINDER | |
| 10 | 1 | HA 6M3K-21.5 | QC TO DRIVER ARM CYLINDER | |
| 11 | 1 | HA 6M3K-35.0 | ARM CYLINDER TO ARM CYLINDER | |
| 12 | 1 | AD 6801 6-6 | 6MJ X 6MB 90 DEG ELBOW | |
| 13 | 2 | HA 8M3K-90.5 | VALVE TO QC HOSE | |
| 14 | 1 | HA 6M3K-80.0 | VALVE TO MLC END | |
| 15 | 1 | HA 6M3K-59.0 | VALVE TO MLC BASE | |
| 16 | 1 | VA 5000-2-COMP | VALVE | 2 SPOOL |
| 17 | 1 | HA 8M3K-15.5 | VALVE TO FILTER | |
| 18 | 1 | AD 2404 10-12 | 10MJ X 12MP | |
| 19 | 1 | GN SP15N*GNO | FILTER HEAD | *1* |
| 20 | 1 | AD 5500-12 | 12 MP X 12 MP 90 | |
| 21 | 2 | AD 8010-15 | MALE HALF QC | |
| 22 | 2 | MI CAPLUG RC 1-1/2 | QC PLUG | |

NOTES: FILTER HEAD PART OF FB-1000 ASSEMBLY