


Charger Plus MNB T R

Specification Guide

The Charger Plus is a portable accessory designed to charge the Radiant miniBTE T R on the go. With built-in lithium-ion technology, a detachable USB-C power cable and power bank, it allows three recharges of the MNB T R

without the need for a power source. Convenient for traveling, the attached lid provides safe storage and transport of hearing instruments, and a drying function controls moisture when the lid is closed.



Packaging set

- Instructions for use
- Power supply plug
- USB cable

Hearing instrument charging times (when completely drained)

- 3.5 h = Fully charged
- 1 h = 40 % charged
- 30 min = 20 % charged

¹ Power plug will vary from country to country
www.sonichearing.ca

Charger Plus MNB T R – Technical data

Charger Plus MNB T R

Designed for/compatibility	Radiant, miniBTE T R
Dimensions	Height 76.4 mm / Width 47.2 mm / Length 95 mm
Weight	180 grams (6.4 oz)
Color	Black
Power supply plug	USB A
Status indications	LED light on charger when plugged to a power supply: Indicates charging status of the power bank. LED light on charger when disconnected from a power supply: Indicates the battery level of the power bank. LED light on hearing aids when charging: Indicates charging mode
Charging time of hearing instruments	Max 3.5 hours depending on initial state of the battery (Temperature: +10 °C to +35 °C [+50 °F to +95 °F]) Max 5 hours depending on initial state of the battery (Temperature: +5 °C to +10 °C [+41 °F to +50 °F] / +35 °C to +38 °C [+95 °F to +100 °F])
Charging time of the power bank battery	Max 4 hours charging depending on initial state of the battery Temperature: +10 °C to +35 °C [+50 °F to +95 °F]
Power source	Supplied power supply unit
Input voltage	5 V DC
Input current	Max 1A [charging internal battery and 2 hearing instruments]
Cable	Detachable cable / 150 cm
Connected to external equipment	When connected to external equipment plugged into a wall outlet, this equipment must comply with IEC-62368 or equivalent safety standards.

Conditions of use

Operating conditions	Temperature: +5 °C to +38 °C [+41 °F to +100 °F] Relative humidity: 5% to 93%, non-condensing
Storage and transportation conditions	Temperature: -25 °C to +60 °C [-13 °F to +140 °F] Relative humidity: 5% to 93%, non-condensing
Atmospheric pressure	700 hPa to 1060 hPa

Technical data: Power supply unit

Input voltage	100 – 240 V AC
Input frequency	50 – 60 Hz
Output voltage	5 V DC
Output current	1 A



Manufacturer

SBO Hearing A/S
Kongebakken 9
DK-2765 Smørum
Denmark

World Headquarters

Sonic Innovations, Inc.
2501 Cottontail Lane
Somerset, NJ 08873
USA
+1 888 423 7834

Imported and Distributed by:

Audmet Canada Ltd
1600 - 4950 Yonge St
Toronto, ON M2N 6K1

www.sonichearing.ca

Sonic is part of the Demant group.

2021-11-23 | 245917 | ver.1.0 | CA-US

